

## FEATURES AND SPECIFICATIONS

The AT-200 (19279-0001) Air Tool is an economical, electrically controlled, air powered termination hand tool. It is designed to provide an effective method for low cost, quality terminations.

- Accepts multiple, inexpensive AT-heads, which provides production flexibility
- Compact design and light weight make this unit ideal for a prototype, repair and small production environment
- Meets ISO standards

### Air Pressure

85-100PSI (At the tool)

5.86 / 6.89 Bar

### Mechanical

Dimensions

Height—247.65mm (9.75")

Width—82.55mm (3.75")

Depth—50.80mm (2.00")

Weight: Gross —1.31kg (2.90 lbs.)

Unpacked —1.06kg (2.35 lbs.)

### Production Rate

Dependent on terminal product selection and operator skill

## AT-200™ Air Tool

19279-0001



## ORDERING INFORMATION

Order No.	Used With	Description
19279-0001	AT-heads, 8-26 AWG*	AT-200 Air Tool
19078-0307	AT-200 Air Tool (19279-0001)	Air Tool Hands-Free Bench Adaptor

\*AT-heads are ordered separately. Each Molex loose part terminal number will have an AT-head linked on the Molex website, if there is a AT-head for that part.

Order No.	Used With	Description
Multiple heads available, please review your Molex loose part terminal number on the Molex web	AT-200 Air Tool†	AT-head

†AT-200 is ordered separately.