

Woodhead Standard Duty Cord Reels

Now with 20A Ratings and CSA Approval 

Woodhead standard duty cord reels, with 35 ft of 12/3 SJTOW cord, now have a 20A rating and are available with multiple end options, including connectors, quad boxes and duplex GFCIs. All models carry CSA listing.



Woodhead 20A Cord Reel

ADVANTAGES AND FEATURES

Models available with 20A ratings

Provides full 20A rating in a cost-effective indoor-rated reel. Eliminates need to specify industrial rated reels to get 20A ratings.

Models available with locking plugs, either NEMA L5-20 or NEMA L5-15

Specified power supply outlets in ceilings utilize locking plugs to prevent disconnection. Factory installed locking plugs eliminate the need for the installer to change the plugs to locking configurations.

Reels complete with connectors; outlet boxes and GFCI ends are CSA listed

Eliminates need for field certifications for installations in Canada.

Available with zero to four outlets

Flying leads allow users to install their own end effects. Factory installed connectors and outlet boxes help get these reels into use quickly.

Powder-coated steel construction

Provides strength and durability to ensure long life.

Simple ball-stop, tension and ratchet adjustment

Simplifies customization to a wide variety of applications.



MARKETS AND APPLICATIONS

Technical Schools / Colleges
Maintenance Shops
Warehouses
Assembly Lines / Manufacturing
Hospitals
Data Centers



Technical School



DataCenter



Warehouse



Assembly Line

Woodhead Standard Duty Cord Reels

Now with 20A Ratings and CSA Approval

SPECIFICATIONS

Reference Information

CSA File No.: LR29921

Physical

Construction: Powder-coated steel
 Cord: All reels include 2 foot primary cord with plug and 35 ft of working cord, 12/3 SJTOW
 Working end: Includes a ball stop and may include a connector or outlet box
 Ratchet lock: Easily disengaged as needed
 Tension: Easily adjusted

Electrical

Voltage: 120V AC

Environmental

Enclosure Rating: NEMA 1

ORDERING INFORMATION

Order No.	Woodhead No.	Plug Type	Current Rating	Working End	No. of Outlets	GFCI Protected
1300910202	<u>998</u>	NEMA 5-20	20A	Flying Leads	--	No
1300910203	998-1533			NEMA 5-20 Connector	1	
1300910204	<u>998-3070G20</u>			Single Duplex GFCI Outlet Box: NEMA 5-20	2	Yes
1300910201	<u>998-3080</u>			Double Duplex Outlet Box: NEMA 5-20	4	No
1300910205	<u>998L</u>	NEMA L5-20: Locking	20A	Flying Leads	--	No
1300910206	<u>998L-2747</u>			NEMA L5-20 Locking Connector	1	
1300910207	<u>998L-3070G20</u>			Single Duplex GFCI Outlet Box: NEMA 5-20	2	Yes
1300910208	<u>998L-1533</u>			NEMA 5-20 Connector	1	No
1300910209	<u>998L-3080</u>			Double Duplex Outlet Box: NEMA 5-20	4	
1300910085	<u>997</u>	NEMA 5-15	15A	Flying Leads	--	No
1300910087	<u>997-1547</u>			NEMA 5-15 Connector	1	
1300910094	<u>997-3070G</u>			Single Duplex GFCI Outlet Box: NEMA 5-15	2	Yes
1300910090	<u>997-3000</u>			Double Duplex Outlet Box: NEMA 5-15	4	No
1300910210	<u>997L</u>	NEMA L5-15: Locking	15A	Flying Leads	--	No
1300910211	<u>997L-2547</u>			NEMA L5-15 Locking Connector	1	
1300910212	<u>997L-3070G</u>			Single Duplex GFCI Outlet Box: NEMA 5-15	2	Yes
1300910213	<u>997L-1547</u>			NEMA 5-15 Connector	1	No
1300910214	<u>997L-3000</u>			Double Duplex Outlet Box: NEMA 5-15	4	

www.molex.com