






High-Speed Networking Solutions

Best-in-Class Data Rates for Seamless Connectivity

PROTOCOLS BY DATA RATE PERFORMANCE

Delivering superior bandwidth and signal integrity, Molex High-Speed Networking Cable solutions are designed to operate across multiple systems and automotive protocols.

PROTOCOLS	HSAUTOLINK I	HSAUTOLINK II	HIGH-SPEED FAKRA MINI (HFM)
			
Data Rate	0-2 Gbps	0-13 Gbps	0-20 Gbps (or 15 GHz)
A2B	✓	✓	
100Base-T1	✓	✓	
USB2.0	✓	✓	
1000Base-T1	✓	✓	
FPD-LINK-II, III, IV		✓	✓
Apix2		✓	✓
GMSL, GMSL2, GMSL3		✓	✓
Apix3			✓
DisplayPort		✓	
USB3.X		✓	
Multi-Gigabit		✓	✓

HFM is a registered trademark of Rosenberger

www.molex.com/highspeednetworking