



### GLOW WIRE PRODUCTS BROCHURE

creating connections for life



#### **Glow Wire Offerings for Signal or Low-Power Products**



Wire-to-Board (under 5.00mm Pitch)

Features	Picoflex	Milli-Grid	Micro-One	RAST 2.5	Mini-Lock	Nano-Fit	KK Plus 250	Micro-Fit	Micro-Fit +	KK Plus 300	CP 3.3	Ultra-Fit	KK Plus 396	Mini Fit-MAX	Mini-Fit	Mini Fit- Sigma
Pitch (mm)	1.27	2.00	2.00	2.50	2.50	2.50	2.50	3.00	3.00	3.00	3.30	3.50	3.96	4.20	4.20	4.20
Voltage (max.)	250V AC	125V AC	250V AC	32 VAC	250 VAC	250 VAC	250 VAC	600V AC	600V AC	250V AC	500V AC	600V AC	350V AC	600V AC	600V AC	600V AC
Operating Temp. (max.)	+105°C	+105°C	+105°C	+120°C	+105°C	+115°C	+105°C	+125°C	+105°C	+105°C	+105°C	+120°C	+105°C	+105°C	+125°C	+105°C
Wire AWG	26 to 28	24 to 30	22 to 28	22 to 24	20 to 26	20 to 26	22 to 28	18 to 30	16 to 30	18 to 20	18 to 28	16 to 22	18 to 20	14 to 16	16 to 28 (+ double crimp)	16 to 24 (+ double crimp)
Current (max.)	1.2A	2.5A	4.0A	6.0A	5.0A	8.0A	6.5A	10.5A	13.0A	11.0A	8.5A	14.0A	11.0A	20.5A	13.0A	13.5A
Circuit Sizes	4 to 26	2 to 10 4 to 50	2 to 8	2 to 20	2 to 15	2 to 8 4 to 16	2 to 8	2 to 12 2 to 24	2 to 8 2 to 22	2 to 4	2, 4, 6	2 to 8 4 to 16	2 to 6	2 to 12	2 to 24	2 to 6 2 to 18
Header Orientation	Vertical	Vertical Right Angle	Vertical Right Angle	Vertical	Vertical Right Angle	Vertical Right Angle	Vertical	Vertical Right Angle	Vertical Right Angle	Vertical	Vertical	Vertical Right Angle	Vertical	Vertical	Vertical Right Angle	Vertical Right Angle
Termination Interface	SMT	Through Hole, SMT	Through Hole, SMT	Through Hole, Card Edge	Through Hole, SMT	Through Hole, SMT	Through Hole	Through Hole, SMT	Through Hole, SMT	Through Hole	Through Hole	Through Hole	Through Hole	Through Hole	Through Hole	-



#### **Glow Wire Offerings for Signal or Low-Power Products**



Wire-to-Board (under 5.00mm Pitch)

Features		Picoflex	Milli-Grid	Micro-One	RAST 2.5	Mini-Lock	Nano-Fit	KK Plus 250	Micro-Fit	KK Plus 300	Micro-Fit +	CP 3.3	Ultra-Fit	KK Plus 396	Mini Fit-MAX	Mini-Fit	Mini Fit-Sigma
Low Halogen			х	х			Х		х	х	х			Х		Х	
UL 94	VO	X	Х	×	Х	×	Х	Х	X	Х	x	X	x	X	Х	х	Х
OL 94	V2				Х												
Row	Single	Х	Х	x	Х	×	×	Х	x	Х	х		×	Х	х		x
KOW	Dual		Х				×		x		х	Х	×		х	Х	x
Disting	Tin	Х	Х	х	Х	×	Х	Х	х	х	х	Х	х	Х	Х	Х	×
Plating	Gold		Х	х			Х		х		х		х			Х	
Locking	Friction	Х	Х		Х												×
Design	Positive		Х	×		×	×	Х	×	х	х	Х	×	Х	х	Х	х
ТРА				х		Х	Х	х	х	х	х	Х	Х	Х	Х	Х	×



# Glow Wire Offerings for High-Power Products Wire-to-Board (over 5.00mm Pitch)



Features	RAST 5	KK 508	Mega-Fit	MLX	CP 6.5	Sabre	Super Sabre
Pitch (mm)	5.00mm	5.08mm	5.70mm	6.35mm	6.50mm	7.50mm	7.50mm
Voltage (max.)	250V AC	600V AC	600V AC	600V AC	600V AC	600V AC	600V AC
Operating Temp. (max.)	+120°C	+105°C	+120°C	+105°C	+105°C	+75°C	+125°C
Wire AWG	18 to 24	18 to 26	10 to 16 (+double crimp)	10 to 20	16 to 26	14 to 24	10 to 12
Current (max.)	16.0A	7.0A	30A	20.0A	10.0 A vertical 11.8 A Right Angle	18.0A	34.0A
Circuit Sizes	2 to 12	2 to 12	2 to 8 2 to 12	2, 3, 4, 6, 9, 12, 15	2, 4, 6	2 to 8	2 to 8
Header Orientation	Vertical Right Angle	Vertical	Vertical Right Angle	Vertical	Vertical Right Angle	Vertical Right Angle	Vertical Right Angle
Termination Interface	Through Hole, Card Edge	Through Hole	Through Hole	Through Hole	Through Hole, SMT	Through Hole	Through Hole



# Glow Wire Offerings for High-Power Products Wire-to-Board (over 5.00mm Pitch)



Features		RAST 5	KK 508	Mega-Fit	MLX	CP 6.5	Sabre	Super Sabre
Low Halogen	Low Halogen							
111.04	VO	х		х		х		
UL 94	V2	х	х		х		х	х
	Single	х	х	×	×		×	х
Row	Dual			х	×	х		
	3 Rows				×			
	Tin	х	х	х	×	х	х	х
Plating	Silver	х						
	Gold			×				
Locking	Friction	х	х					
Locking Design	Positive			×	×	×	×	х
ТРА				×		×		



## **Glow Wire Offerings for Signal or Low-Power Products Wire-to-Wire**



Features	Standard 0.062"/0.062"+	CP 4.5	CP 6.5	Standard .093	VersaBlade	VersaBlade HT	
Pitch (mm)	3.68	4.50	6.5	5.03 6.30 6.70	6.20	6.20	
Voltage (max.)	250V AC	600V AC 600 VAC		600V AC	600V AC	600V AC	
Operating Temp. (max.)	+105°C	+120°C	+105°C +105°C		105°C+	+150°C	
Wire AWG	16 to 30	16 to 26	16 to 26	14 to 22 (+double crimp)	14 to 24 (+double crimp)	14 to 22 (+double crimp)	
Current (max.)	11.5A	10.0A	12.5A	17.0A	15.0A	14.0A	
Circuit Sizes	<b>Circuit Sizes</b> 2, 4, 9, 12		2, 4, 6	2, 4, 15	1 to 9	2,3,4	



## **Glow Wire Offerings for Signal or Low-Power Products Wire-to-Wire**



Features		Standard .062"/.062"+	CP 4.5	CP 6.5	Standard .093"	VersaBlade	VersaBlade HT
Low Halogen			х		×		
UL 94	V0	×	х	x		×	х
OL 94	V2				х		
Row	Single	×			х	x	х
	Dual	x	x	x		x	х
	3 Rows	×			х		
Plating	Tin	×	х	х	х	х	х
Plating	Gold	х			х		
Locking	Friction	х					
Locking Design	Positive		х	х	х	х	×
ТРА			х	Х		х	х