



**Low-OH Core  
Hard Cladding  
High NA**

**Polymicro  
SILICA/HARD  
POLYMER CLAD  
Optical Fiber JTFLH**

## CHARACTERISTICS

Step index	Low-OH core for Vis-NIR transmission	Operating temperature: -65 to +140°C
Numerical aperture: 0.37 ± 0.02 and 0.48 ± 0.02	Sterilizable and bio-compatible – USP class VI*	
Low-OH core, PolyClad® hard polymer clad	Standard buffer: Tefzel®	High-OH and custom sizes available
	Custom buffer: Acrylate, Nylon, Hytrel®	

**Typical Attenuation**



\* The end manufacturer is responsible for bio-compatibility and sterilization testing and validation studies. Tefzel® and Hytrel® are registered trademarks of DuPont Corporation.

## Specifications

### JTFLH – TEFZEL® BUFFER 0.37NA

Product Descriptor	Core (µm)	Clad (µm)	Buffer (µm)	Short-term Bend Radius (mm)	Long-term Bend Radius (mm)
JTFLH200230500	200 ± 4	230 +0/-10	500 ± 30	20	25
JTFLH300330650	300 ± 6	330 +5/-10	650 ± 30	30	35
JTFLH400430730	400 ± 8	430 +5/-10	730 ± 30	40	50
JTFLH6006301040	600 ± 10	630 +5/-10	1040 ± 30	50	75
JTFLH8008301040	800 ± 10	830 ± 10	1040 ± 30	75	100
JTFLH100010351400	1000 ± 15	1035 ± 15	1400 ± 50	90	120
JTFLH150015352000	1500 ± 15	1535 ± 15	2000 ± 50	76	253

### JTFLH – TEFZEL® BUFFER 0.48NA

Product Descriptor	Core (µm)	Clad (µm)	Buffer (µm)	Short-term Bend Radius (mm)	Long-term Bend Radius (mm)
JTFLH200230500	200 ± 4	230 +0/-10	500 ± 30	20	25
JTFLH300330650	300 ± 6	330 +5/-10	650 ± 30	30	35
JTFLH400430730	400 ± 8	430 +5/-10	730 ± 30	40	50
JTFLH6006301040	600 ± 10	630 +5/-10	1040 ± 30	50	75
JTFLH8008301040	800 ± 10	830 ± 10	1040 ± 30	75	100
JTFLH100010351400	1000 ± 15	1035 ± 15	1400 ± 50	90	120
JTFLH150015352000	1500 ± 15	1535 ± 15	2000 ± 50	76	253

**Note:** The items listed in this table are standard configurations and sizes. Other configurations may be available on request.

**Tell us how we can assist with your projects. Molex-your resource in optical fiber.**

[www.molex.com/polymicro](http://www.molex.com/polymicro)