

# SlimStack Board-to-Board Connectors, 0.35 and 0.80mm Pitch, Battery Series >



Achieve up to 18.0A of power and electrical reliability in an ultra-compact design with SlimStack Hybrid Power Connectors, designed for battery and other power applications.

As consumers continue to demand smaller devices and bigger current value, the need for microminiature designs grows. Hybrid connectors deliver design flexibility while meeting tight-packaging needs.

## FEATURES AND ADVANTAGES

### Delivers up to 18.0A power

Meets the growing power needs of tight-packaging applications

### Compact hybrid interface with power and signal contacts

Combines extra signal lines into a power connector footprint for space savings

### Robustness with full metal cover

Prevents housing damage during mating with interior cover

### Dual-contact design

Assures contact reliability

### Delivers up to 6.0A




Receptacle, 505004 Series

### Delivers up to 11.0A




Receptacle, 207419 Series

### Delivers up to 15.0A



Receptacle, 216656 Series


### Delivers up to 18.0A



Receptacle, 220250 Series

### Wide alignment area

Provides easy and secure mating




Plug, 505006 Series




Plug, 207420 Series

### Armor nail

Prevents damage to housing



Plug, 216657 Series



Plug, 220251 Series

# SlimStack Board-to-Board Connectors, 0.35 and 0.80mm Pitch, Battery Series >


## APPLICATIONS

### Mobile Devices

Smartphones  
Tablet PCs  
Wearable Devices  
Portable Audio  
Portable Navigation Equipment

### Medical Devices

Patient Monitoring  
Therapeutic and Surgical



Smartphone



Wearable Watch



Patient Monitoring

## SPECIFICATIONS

### REFERENCE INFORMATION

Packaging: Embossed Tape on Reel  
Designed In: Millimeters  
RoHS: Yes  
Halogen Free: Low-Halogen

### ELECTRICAL

Voltage (max.): 50V  
Current (max.):  
[505004/505006](#)  
Signal Contact: 0.3A per circuit  
Power Contact: 3.0A per circuit  
[207419/207420](#)  
Signal Contact: 0.3A per circuit  
Power Contact: 5.5A per circuit  
[216656/216657](#)  
Signal Contact: 0.3A per circuit  
Power Nail/1 pin + Power Contact/2 pin: 15.0A  
[220250/220251](#)  
Signal Contact: 0.3A per circuit  
Power Nail/1 pin + Power Contact/2 pin: 18.0A

### ELECTRICAL

Contact Resistance (max.):  
[505004/505006](#)  
Signal Contact: 80 milliohms  
Power Contact: 10 milliohms  
[207419/207420](#)  
10 milliohms  
[216656/216657](#)  
Signal Contact: 50 milliohms  
Power Nail/Power Contact: 5 milliohms  
[220250/220251](#)  
Signal Contact: 50 milliohms  
Power Nail/Power Contact: 5 milliohms

Dielectric Withstanding Voltage: 250V AC  
Insulation Resistance (min.): 100 Megohms

### MECHANICAL

Durability (max.): 10 cycles

### PHYSICAL

Housing: LCP, UL94V-0, Black  
Contact: Copper Alloy  
Plating:  
Contact Area – Gold  
Solder Tail Area – Gold  
Underplating – Nickel  
Operating Temperature: -40 to +85° C

# SlimStack Board-to-Board Connectors, 0.35 and 0.80mm Pitch, Battery Series >

## ORDERING INFORMATION

Order No.		Circuits	Current (A)	Signal Pitch (mm)	Mated Height (mm)	Mated Width (mm)	Length (mm)
Receptacle	Plug						
220250-0069	220251-0069	8 (6 Signal; 2 Power)	18.0	0.35	0.70	2.30	5.10
216656-0109	216657-0109	10 (6 Signal; 4 Power)	15.0	0.40			5.00
207419-0081	207420-0081	8 (4 Signal; 4 Power)	11.0	0.80	0.75	2.50	5.20
505004-0812	505006-0812	8 (4 Signal; 4 power)	6.0	0.40	0.75	2.50	4.20

\*Maximum current of 15.0A per connector is applicable if the circuit is constructed by two power circuits and one power nail via a PWB/FPC circuit.

\*Maximum current of 11.0/10.0/6.0A per connector is applicable if the circuit is constructed by two power circuits via a PWB/FPC circuit.

[www.molex.com/link/slimstack.html](http://www.molex.com/link/slimstack.html)