

Application Tooling Manual PPDLH

molex[®]

Putt Pump DielessHead Crimper for Insulated and Non-Insulated Terminals and Splices

Features and Benefits

Crimps a wide range of products and does not require die set changes, which reduces the overall cost and provides production flexibility

Swivel base and terminal locator included to provide the operator with a user-friendly tool to increase productivity

Complete lightweight system that allows tool to be moved and stored easily



Specifications

REFERENCE INFORMATION

Pneumatic: Supply Pressure

-100 PSI

Air Pressure -125 PSI max.

Cycle Time: 15 seconds

Ordering Information

| Order No. | Wire Gauge (AWG) | Operating Pressure* |
|------------|------------------|---------------------|
| 63816-1700 | 8 | 40 PSI |
| | 6 | 45 PSI |
| | 4 | 50 PSI |
| | 2 | 55 PSI |
| | 1 | 65 PSI |
| | 1/0 | 65 PSI |
| | 2/0 | 70 PSI |
| | 3/0 | 75 PSI |
| | 4/0 | 75 PSI |
| | 250MCM | 85 PSI |
| | 300MCM | 90 PSI |
| | 350MCM | 90 PSI |
| | 400MCM | 100 PSI |
| 500MCM | 100 PSI | |

* The pressure settings shown in the chart refer to the SPX power team pump that is currently shipped with the PPDLH tool. Please review the instructions sent with your specific tool.

www.molex.com/link/ppdlh.html