

# Brad EtherNet/IP CIP Safety HarshIO Modules

Featuring CIP Safety technology, Brad EtherNet/IP CIP Safety HarshIO Modules are IP67 IO modules designed for connecting industrial safety controllers to sensors and actuators in harsh duty environments to permit the durable and reliable automation of safety systems.



## FEATURES AND ADVANTAGES

### Permits on-machine installation in harsh environments, withstanding shock, high vibration and high temperatures without the need for a protective cabinet

Module is IP67-rated for dust and water resistance, is potted with resin and uses metallic connectors

### Helps ensure safety and reliability with TÜV- and ODVA-certified design

Conforms to EN 61508 SIL3 and Cat4 PLe according to ISO 13849-1 with a mission time exceeding 20 years

### Enhances versatility and design flexibility with multiple options available

Options include 4- or 5-pin Mini-Change power connectors, 12 safe inputs plus 2 bipolar or 4 sourcing safe outputs, connection of single- or dual-channel safety devices and can connect to both standard and safety-rated sensors

### Reduces commissioning time with Ultra-Lock™ M12 push-to-lock technology

Uses the fastest, easiest and most secure M12 connection solution and accepts both threaded cordsets and Ultra-Lock™ connectors

IP Rating	IP67
Current	1A (4 sourcing outputs) or 2A (2 bipolar outputs)
Voltage	24V DC, -15/+20%
Connectors	4- or 5-pole Mini-Change
Mounting	60mm on-machine
Operating Temperature	-25 to +70°C (industrial-grade) or 0 to +60°C (commercial-grade)

### Speeds module replacement while eliminating special tools or recommissioning

Overmolded memory key stores the module's configuration

### Enables the use of daisy-chain wiring to wire an entire application without switches

Integrated two-port switch design and DLR support for Ethernet redundancy permits cost savings thanks to simplified system design

### Allows easy installation with Rockwell Automation-ready design

Full integration into RA Logix Designer™ with GuardLogix™ controllers (FW>v32); upload EDS file from module using RSLinx

### Meets environmental demands with commercial- and industrial-grade options

Modules are available in commercial-grade options or industrial-grade options that are capable of operation in -25 to +70°C temperature ranges

### Allows simple configuring and diagnosing HarshIO safety module using free Molex SNCT software

Features include HarshIO online discovery, copy-and-paste ability to and from RA Logix Designer™ (SNN, Signature), safety lock and password protection

### Permits users to quickly and easily determine status

Diagnostic LEDs indicate network, IO and power conditions

# Brad EtherNet/IP CIP Safety HarshIO Modules >

## MARKETS AND APPLICATIONS

### Automotive

Assembly lines  
Body shops  
Material handling equipment

### Industrial Automation

Complex machines  
CNC machines  
Robotics  
Agricultural and food industry equipment  
Medical/pharmaceutical machines



Assembly Lines



CNC Machines



Robotics

## SPECIFICATIONS

### Reference Information

Designed in: Millimeters  
TÜV Certified: Yes  
ODVA Conforming: Yes  
RoHS: Yes  
CE: Yes  
REACH: Yes  
UL/cUL: Yes  
China CCC: Yes  
Industrial Grade Versions: Korean CC, UK CA

### Physical

Dimensions: 238.00 x 60.00 x 48.00mm  
Housing: IP67-rated  
Operating Temperatures:  
Industrial-grade: -25 to +70°C  
Commercial-grade: 0 to +60°C  
Storage Temperature: -40 to +70°C  
Relative Humidity: 10 to 95%, non-condensing  
Overmolded Memory Key: Internal or M8

### Digital Inputs

Safety Inputs (PNP): 12  
Test Pulses: 12  
Diagnostic LEDs: Yes  
Protection: Short circuit and overcurrent  
Sensor Power Supply: 700mA per sensor  
Input Delay: On-off and off-on  
Connector: M12, 5-pin, female, Stainless Steel

### Digital Outputs

Safety Outputs: 2 bipolar or 4 sourcing  
Output Current (max.):  
Sourcing: 1A per channel  
Bipolar: 2A per dual channel (current sourcing/  
current sinking pair)  
Pulse Test: Configurable  
Diagnostic LEDs: Yes  
Protection: Short circuit and overcurrent  
Output Delay: On-off and off-on

### Standard Outputs or Pulse Test Output

Outputs: 12  
Output Current: 700mA  
Protection: Short circuit and overcurrent

### Shock and Vibration

Vibration: MIL-STD-202F, method 204D  
Mechanical Shock: MIL-STD-202F, method  
213B  
Thermal Shock: MIL-STD-1344A

### Fieldbus

EtherNet/IP CIP Safety Adapter: Yes  
ODVA CIP Safety I/O Generic Profiles: Yes  
I/O Update Rate: Up to 10ms (RPI)  
Data Access:  
Implicit messages (for I/O data)  
Explicit messages (for read/write module  
configuration and diagnostic)  
ACD: Yes  
IP Address Capabilities:  
DHCP, Static  
Address, EtherNet/IP 0xF5/0xF6 objects  
EDS Upload Service: Yes

### Power Connectors

Power In: Male Mini-Change, 4- or 5-pole  
Power Out: Female Mini-Change, 4- or 5-pole  
Protection: Power crossing

### Power Requirements

Module Input Power: 24V DC (-15/+20%)  
Module Output Power: 24V DC (-15/+20%),  
8.0A max. per module

### Ethernet Switch

Switch: 2-port, 10/100-Mbps  
(auto-negotiation), full duplex,  
Storm Protection  
DLR Client: Yes

# Brad EtherNet/IP CIP Safety HarshIO Modules

## ORDERING INFORMATION

Series No.	Power Connector	Description	Memory Key	Operating Temperature	I/O Inputs	I/O Outputs
<a href="#">112095</a>	7/8" 4-pin	Industrial-grade EtherNet/IP CIP Safety HarshIO Digital Module	Internal Window Key or External M8 Key	-25 to +70°C	12 (PNP)	4 (sourcing) or 2 (bipolar)
	7/8" 5-pin					
	7/8" 4-pin	Commercial-grade EtherNet/IP CIP Safety HarshIO Digital Module	Internal Window Key or External M8 Key	0 to +60°C		